



## **Pump Discharge Hoses**



#### Pump Discharge Hose Ø 6 mm

ACC00909 : 5 m - ACC00910 : 50 m - ACC00914 : reinforced, 50 m Clear PVC tubing for connecting the pump to the discharge outlet i.d. 6 mm (1/4")



Pump Discharge Hose ⊘ 10 mm ACC00911 : 25 m - ACC00915 : reinforced, 25 m

Clear PVC tubing for connecting the pump to the discharge outlet i.d. 10 mm (3/8")

#### **Connectors**



# Straight and elbow connectors

ACC00900 : for Ø 6 mm hose - ACC00901 : for Ø 10 mm hose Straight and elbow connectors for connecting hoses together.



ACC00902: Ø 6 mm - ACC00903: Ø 6 mm

To make the connection between 3 tubes. For tubes Ø 6 mm int. (1/4 '')



### Self Sealing Fitting

ACC00919 : for use with  $\emptyset$  6 mm tubing - ACC00920 : for use with  $\emptyset$  10 mm tubing.

Self sealing fittings for condensate discharge tubing.

### **Spare Parts**



### Detection unit

SI2958

For replacing the detection unit when necessary. Si-30, Si-33, PE 5200



ACC00925

For replacing the non-return valve when necessary in Si-83, SI 1830.



#### Replacement tube

PE5002

Replacement tube of the peristaltic pumps PE 5000, PE 5100 and PE 5200.